

352 DS AIREX 1V - AIR POWERED EXPLOSION PROOF



CHEMICAL-PHARMACEUTICAL









- areas









✓ Integrated filter cleaning system

use of disposable bags

✓ Compact and mobile

✓ Easy filter replacement

✓ Extractable collection container with optional

✓ Vacuum gauge to detect filter clogging



Continue of the continue of th
•

- ✓ Compressed air supply through a single
- ✓ Earth grounding
- ✓ Certificate for use in ATEX 1,2,21 and 22

SUCTION UNIT		
Atex zones		ATEX Z1-2/21-22
Marking	Ex II 2D Ex h IIIC T85°C Db	- Ex II 2G Ex h IIB T6 Gb
Air supply	lt/min	1500
Air supply pressure	bar	6
Ø Air supply hose	mm	10
Max water lift	mmH2O	4180
Max air flow	m³/h	150
Suction inlet	mm	80
Noise level (EN ISO 3744)	dB(A)	73
FILTER UNIT		
Filter Type		Star
Surface - Diameter	cm²-mm	20.000 - 420
Material - Efficiency	IEC 60335-2-69	Polyester - ANT M
Cleaning system		Manual
COLLECTION UNIT		
Capacity	lt.	80
VOLUME		
Dimensions	cm	70x55x127h
Weight	kg	50





SUCTION UNIT

The suction is provided by a venturi compressed-air-driven suction unit, protected inside a strong steel chassis, which contains also sound absorbing material to minimize noise during service. The suction is developed by a venturi-type vented suction unit, protected inside a solid steel head, containing sound absorbing material that minimizes noise during service.

The head includes a pressure and a vacuum gauge, in order to detect the clogging of the filter



FILTER UNIT

The large surface star filter, located inside the filter stainsteel chamber, is made of polyester and provides high resistance against clogging and passage of fine dust.

It is possible to clean the filter using an integrated mechanical system: an external lever shakes the filter vertically and enables to clean the filter thoroughly and safely, maintaining constant suction performance and preventing any dispersion of dust in the environment.



COLLECTION UNIT

The vacuum is assembled onto a sturdy steel chassis, and provided with industrial quality wheels, that make it suitable for mobile service even when used on rough surfaces. The vacuumed material is placed inside an AISI304 stainless steel drop-down bin mounted on wheels, which makes it possible to dispose easily and safely of the vacuumed material, if need be collecting it directly into a paper bag.



- ✓ ABSOLUTE HEPA FILTER /H14
- ✓ TOTAL STAINLESS STEEL CONSTRUCTION
- CYCLONE FOR FILTER PROTECTION
- PRESSURE DIFFERENTIAL KIT FOR USE OF DISPOSABLE BAG