



# SEP.DC-001

PRESEPARATOR FOR MEDIUM TOXIC PHARMACEUTICAL DUST



Filter category:

## FEATURES

Available in a WIP (Wash-in-Place) version to deactivate dust on internal surfaces

Pre-separator cyclone without filter, AISI316 stainless steel, polished inside and outside. AISI304 trolley

Dust separation efficiency with cyclone at 98%

Cleaning operations are performed safely and quickly to ensure operator safety

Delfin units guarantee a significant reduction in costs

All data mentioned in this document may change without notice. All data contained in this document is subject to change without notice.

**DELFIN**  
FOR A DUST-FREE WORLD  
[www.delfinvacuums.com](http://www.delfinvacuums.com)  
[delfin@delfinvacuums.it](mailto:delfin@delfinvacuums.it)

COPYRIGHT 2026 DELFIN S.R.L. ALL RIGHTS RESERVED  
COPYRIGHT 2026 DELFIN S.R.L. ALL RIGHTS RESERVED

## TECHNICAL DATA

		SEP.DC-001
Suction inlet diameter	mm	3"
Tank capacity	L.	25
Dimensions	cm	72x75x240h
Weight	kg	65
Maximum air flow	m <sup>3</sup> /h	1000

## OPTIONAL

Code	Description
WIP	Washing in place



MACHINE CODE	DESCRIPTION
SEP.DC-001	SEP. X X X D220 SC/FARF6" LVL.C CARR.TO 30LT.

All data mentioned in this document may change without notice. All data contained in this document is subject to change without notice.

**DELFIN**  
FOR A DUST-FREE WORLD

[www.delfinvacuums.com](http://www.delfinvacuums.com)  
[delfin@delfinvacuums.it](mailto:delfin@delfinvacuums.it)