



# SEP.DC-002

PRESEPARATOR FOR MEDIUM TOXIC PHARMACEUTICAL DUST



Filter category:

## FEATURES

Available in a WIP (Wash-in-Place) version to deactivate dust on internal surfaces

Pre-separator cyclone without filter, AISI316 stainless steel, polished inside and outside. AISI304 trolley

Dust separation efficiency with cyclone at 98%

Cleaning operations are performed safely and quickly to ensure operator safety

Delfin units guarantee a significant reduction in costs

## TECHNICAL DATA

		SEP.DC-002
Suction inlet diameter	mm	3"
Tank capacity	L.	40
Dimensions	cm	72x75x175h
Weight	kg	55
Maximum air flow	m <sup>3</sup> /h	1000

## OPTIONAL

Code	Description
WIP	Washing in place



MACHINE CODE	DESCRIPTION
SEP.DC-002	SEP. X X C/CYCLONE D220 CARR.TO C/CONT. 40LT.

All data mentioned in this document may change without notice. All data contained in this document is subject to change without notice.

**DELFIN**  
FOR A DUST-FREE WORLD

www.delfinvacuums.com  
delfin@delfinvacuums.it